

Cell	Model name	Size(mm) (W x H x L)	Weight (kg)	H2 Flow rate (L/min)	H2 Flow rate (Nm <sup>3</sup> /h)	H2 Flow rate (g/h)	O2 Flow rate (L/min)
1	LBE-PMC	162 X 177 X 94	7.55	1.14	0.0684	6.156	0.57
2	LBE-P2MC	162 X 177 X 99	7.90	2.28	0.1368	12.312	1.14
3	LBE-P3MC	162 X 177 X 104	8.25	3.42	0.2052	18.468	1.71
4	LBE-P4MC	162 X 177 X 109	8.60	4.56	0.2736	24.624	2.28
5	LBE-P5MC	162 X 177 X 114	8.95	5.70	0.3420	30.780	2.85
6	LBE-P6MC	162 X 177 X 119	9.30	6.84	0.4104	36.936	3.42
7	LBE-P7MC	162 X 177 X 124	9.65	7.98	0.4788	43.092	3.99
8	LBE-P8MC	162 X 177 X 129	10.00	9.12	0.5472	49.248	4.56
9	LBE-P9MC	162 X 177 X 134	10.35	10.26	0.6156	55.404	5.13
10	LBE-P10MC	162 X 177 X 139	10.70	11.40	0.6840	61.560	5.70
11	LBE-P11MC	162 X 177 X 144	11.05	12.54	0.7524	67.716	6.27
12	LBE-P12MC	162 X 177 X 149	11.40	13.68	0.8208	73.872	6.84
13	LBE-P13MC	162 X 177 X 154	11.75	14.82	0.8892	80.028	7.41
14	LBE-P14MC	162 X 177 X 159	12.10	15.96	0.9576	86.184	7.98
15	LBE-P15MC	162 X 177 X 164	12.45	17.10	1.0260	92.340	8.55
16	LBE-P16MC	162 X 177 X 169	12.80	18.24	1.0944	98.496	9.12
17	LBE-P17MC	162 X 177 X 174	13.15	19.38	1.1628	104.652	9.69
18	LBE-P18MC	162 X 177 X 179	13.50	20.52	1.2312	110.808	10.26
19	LBE-P19MC	162 X 177 X 184	13.85	21.66	1.2996	116.964	10.83
20	LBE-P20MC	162 X 177 X 189	14.20	22.80	1.3680	123.120	11.40
21	LBE-P21MC	162 X 177 X 194	14.55	23.94	1.4364	129.276	11.97
22	LBE-P22MC	162 X 177 X 199	14.90	25.08	1.5048	135.432	12.54
23	LBE-P23MC	162 X 177 X 204	15.05	26.22	1.5732	141.588	13.11
24	LBE-P24MC	162 X 177 X 209	15.40	27.36	1.6416	147.744	13.68
25	LBE-P25MC	162 X 177 X 214	15.95	28.50	1.7100	153.900	14.25
26	LBE-P26MC	162 X 177 X 219	16.30	29.64	1.7784	160.056	14.82
27	LBE-P27MC	162 X 177 X 224	16.65	30.78	1.8468	166.212	15.39
28	LBE-P28MC	162 X 177 X 229	17.00	31.92	1.9152	172.368	15.96
29	LBE-P29MC	162 X 177 X 234	17.35	33.06	1.9836	178.524	16.53
30	LBE-P30MC	162 X 177 X 239	17.70	34.20	2.0520	184.680	17.10
31	LBE-P31MC	162 X 177 X 244	18.05	35.34	2.1204	190.836	17.67
32	LBE-P32MC	162 X 177 X 249	18.40	36.48	2.1888	196.992	18.24
33	LBE-P33MC	162 X 177 X 254	18.75	37.62	2.2572	203.148	18.81
34	LBE-P34MC	162 X 177 X 259	19.10	38.76	2.3256	209.304	19.38
35	LBE-P35MC	162 X 177 X 264	19.45	39.90	2.3940	215.460	19.95
36	LBE-P36MC	162 X 177 X 269	19.80	41.04	2.4624	221.616	20.52
37	LBE-P37MC	162 X 177 X 274	20.15	42.18	2.5308	227.772	21.09
38	LBE-P38MC	162 X 177 X 279	20.50	43.32	2.5992	233.928	21.66
39	LBE-P39MC	162 X 177 X 284	20.85	44.46	2.6676	240.084	22.23
40	LBE-P40MC	162 X 177 X 289	21.20	45.60	2.7360	246.240	22.80
41	LBE-P41MC	162 X 177 X 294	21.55	46.74	2.8044	252.396	23.37
42	LBE-P42MC	162 X 177 X 299	21.90	47.88	2.8728	258.552	23.94
43	LBE-P43MC	162 X 177 X 304	22.25	49.02	2.9412	264.708	24.51
44	LBE-P44MC	162 X 177 X 309	22.60	50.16	3.0096	270.864	25.08
45	LBE-P45MC	162 X 177 X 314	22.95	51.30	3.0780	277.020	25.65
46	LBE-P46MC	162 X 177 X 319	23.30	52.44	3.1464	283.176	26.22
47	LBE-P47MC	162 X 177 X 324	23.65	53.58	3.2148	289.332	26.79
48	LBE-P48MC	162 X 177 X 329	24.00	54.72	3.2832	295.488	27.36
49	LBE-P49MC	162 X 177 X 334	24.35	55.86	3.3516	301.644	27.93
50	LBE-P50MC	162 X 177 X 339	24.70	57.00	3.4200	307.800	28.50