

Cell	Model name	Size(mm) (L x W x H)	Weight (kg)	H2 Flow rate (L/min)	H2 Flow rate (Nm ³ /h)	H2 Flow rate (g/h)	O2 Flow rate (L/min)
1	LBE-1C	265 X 265 X 27	10.10	0.70	0.042	3.78	0.35
2	LBE-2C	265 X 265 X 33	10.82	1.40	0.084	7.56	0.70
3	LBE-3C	265 X 265 X 39	11.55	2.10	0.126	11.34	1.05
4	LBE-4C	265 X 265 X 45	12.28	2.80	0.168	15.12	1.40
5	LBE-5C	265 X 265 X 51	13.01	3.50	0.210	18.90	1.75
6	LBE-6C	265 X 265 X 57	13.74	4.20	0.252	22.68	2.10
7	LBE-7C	265 X 265 X 63	14.47	4.90	0.294	26.46	2.45
8	LBE-8C	265 X 265 X 69	15.20	5.60	0.336	30.24	2.80
9	LBE-9C	265 X 265 X 75	15.93	6.30	0.378	34.02	3.15
10	LBE-10C	265 X 265 X 81	16.66	7.00	0.420	37.80	3.50
11	LBE-11C	265 X 265 X 87	17.39	7.70	0.462	41.58	3.85
12	LBE-12C	265 X 265 X 93	18.12	8.40	0.504	45.36	4.20
13	LBE-13C	265 X 265 X 99	18.85	9.10	0.546	49.14	4.55
14	LBE-14C	265 X 265 X 105	19.58	9.80	0.588	52.92	4.90
15	LBE-15C	265 X 265 X 111	20.31	10.50	0.630	56.70	5.25
16	LBE-16C	265 X 265 X 117	21.04	11.20	0.672	60.48	5.60
17	LBE-17C	265 X 265 X 123	21.77	11.90	0.714	64.26	5.95
18	LBE-18C	265 X 265 X 129	22.50	12.60	0.756	68.04	6.30
19	LBE-19C	265 X 265 X 135	23.23	13.30	0.798	71.82	6.65
20	LBE-20C	265 X 265 X 141	23.96	14.00	0.840	75.60	7.00
21	LBE-21C	265 X 265 X 147	24.69	14.70	0.882	79.38	7.35
22	LBE-22C	265 X 265 X 153	25.42	15.40	0.924	83.16	7.70
23	LBE-23C	265 X 265 X 159	26.15	16.10	0.966	86.94	8.05
24	LBE-24C	265 X 265 X 165	26.88	16.80	1.008	90.72	8.40
25	LBE-25C	265 X 265 X 171	27.61	17.50	1.050	94.50	8.75
26	LBE-26C	265 X 265 X 177	28.34	18.20	1.092	98.28	9.10
27	LBE-27C	265 X 265 X 183	29.07	18.90	1.134	102.06	9.45
28	LBE-28C	265 X 265 X 189	29.80	19.60	1.176	105.84	9.80
29	LBE-29C	265 X 265 X 195	30.53	20.30	1.218	109.62	10.15
30	LBE-30C	265 X 265 X 201	31.26	21.00	1.260	113.40	10.50
31	LBE-31C	265 X 265 X 207	31.99	21.70	1.302	117.18	10.85
32	LBE-32C	265 X 265 X 213	32.72	22.40	1.344	120.96	11.20
33	LBE-33C	265 X 265 X 219	33.45	23.10	1.386	124.74	11.55
34	LBE-34C	265 X 265 X 225	34.18	23.80	1.428	128.52	11.90
35	LBE-35C	265 X 265 X 231	34.91	24.50	1.470	132.30	12.25
36	LBE-36C	265 X 265 X 237	35.64	25.20	1.512	136.08	12.60
37	LBE-37C	265 X 265 X 243	36.37	25.90	1.554	139.86	12.95
38	LBE-38C	265 X 265 X 249	37.10	26.60	1.596	143.64	13.30
39	LBE-39C	265 X 265 X 255	37.83	27.30	1.638	147.42	13.65
40	LBE-40C	265 X 265 X 261	38.56	28.00	1.680	151.20	14.00
41	LBE-41C	265 X 265 X 267	39.29	28.70	1.722	154.98	14.35
42	LBE-42C	265 X 265 X 273	40.02	29.40	1.764	158.76	14.70
43	LBE-43C	265 X 265 X 279	40.75	30.10	1.806	162.54	15.05
44	LBE-44C	265 X 265 X 285	41.48	30.80	1.848	166.32	15.40
45	LBE-45C	265 X 265 X 291	42.21	31.50	1.890	170.10	15.75
46	LBE-46C	265 X 265 X 297	42.94	32.20	1.932	173.88	16.10
47	LBE-47C	265 X 265 X 303	43.67	32.90	1.974	177.66	16.45
48	LBE-48C	265 X 265 X 309	44.40	33.00	1.980	178.20	16.50